

UPH/EC

Mobile air purifying units









Mobile air purification units with EC Technology motors and a 25 mm thick acoustically insulated casing to reduce noise.

Characteristics:

- 40 mm aluminium profile structure.
- · Wheel kit.
- Plug & Play system with integrated control.
- Covers with a high quality, 25 mm thick acoustic casing made of prefinished sheet.
- · Backward curved impeller.
- Filtration stages, depending on model:
- F9.
- HEPA H14.
- · Active carbon filter for odour removal.
- · Adjustable filter change alarm.
- Germicidal chamber with UVc ultraviolet lamps (256 nm), depending on model.
- Inspection cover for filter maintenance and replacement.

• Air inlet nozzle with diffusers that increase the efficiency of the fan.

Motor:

- High efficiency external rotor EC Technology motors, adjustable via 0-10 V signal.
- Single phase 200-240 V 50/60 Hz.
- Maximum temperature of air to be carried:
 -25 °C +60 °C.


Finish:

 Structure of anodised aluminium profiles and pre-lacquered sheet metal with 25 mm thermal and acoustic insulation panels.

On request:

- Particle sensor for automatic control.
- · Different stages of filtration.

Order code



Filter characteristics

Filters	EN 779 <i>Em</i>	EN 1822	ISO 16890			
		-	ISO ePM₁	ISO ePM _{2,5}	ISO ePM ₁₀	ISO COARSE
F9	95%	-	>80%	>95%	>95%	-
HEPA H14	-	>99.995%	-	-	-	-

Technical characteristics

Model	Recommended Model effective working area¹(m²)		Speed	Maximum Power supply power		Sound pressure level at 50% of max speed. ²	Maximum flow rate (m³/h)		Approx. weight
	Filters (F9)	Filters (H14)	(r/min)	(W)		dB (A)	Filters (F9)	Filters (H14)	(Kg)
UPH/EC-220	50	-	3265	176	200-240V 50/60Hz 1Ph	48	420	-	32
UPH/EC-250	60	-	2850	180	200-240V 50/60Hz 1Ph	49	500	-	33
UPH/EC-310	65	55	1920	175	200-240V 50/60Hz 1Ph	47	550	450	34
UPH/FC-400	190	155	1550	460	200-240V 50/60Hz 1Ph	47	1600	1300	 68

¹Recommended effective working area with a 3-meter-high premises.

 $^{^{\}rm 2}$ Irradiated sound pressure level in dB(A) at a distance of 3 m.

Technical characteristics of the UVc germicidal chamber

According to the model, these purification units can integrate a germicidal chamber, built with UVc ultraviolet lamps in a 256 nm spectrum, a wave width indicated to inactivate a wide variety of microorganisms by absorbing short wavelength energy through DNA and RNA.



Model	Number of lamps	Total electrical power (W)	Total Uvc radiation power (W)	Radiation dose (mJ/ cm²) *
UPH/EC-220	6	54	16.8	7.2
UPH/EC-250	6	54	16.8	6.0
UPH/EC-310	6	54	16.8	6.7
UPH/EC-400	4	102	28	5.4

Minimum dose calculated based on the maximum flow rate.



Erp. (Energy Related Products)

Information on Directive 2009/125/EC can be downloaded from the SODECA website or the QuickFan selector programme.

Dimensions mm



	Α	В	н
UPH/EC-220	500	542	642
UPH/EC-250	500	542	642
UPH/EC-310	500	542	642
UPH/EC-400	700	742	842

Data subject to change without prior notice.